

# Огнетушители, шкафы для безопасного хранения CARL ROTH Q-CLASSIC-90, SEKUROKA, K-PHOENIX-90, SL-Classic, G90

## Технические характеристики

**Алматы** (7273)495-231  
**Ангарск** (3955)60-70-56  
**Архангельск** (8182)63-90-72  
**Астрахань** (8512)99-46-04  
**Барнаул** (3852)73-04-60  
**Белгород** (4722)40-23-64  
**Благовещенск** (4162)22-76-07  
**Брянск** (4832)59-03-52  
**Владивосток** (423)249-28-31  
**Владикавказ** (8672)28-90-48  
**Владимир** (4922)49-43-18  
**Волгоград** (844)278-03-48  
**Вологда** (8172)26-41-59  
**Воронеж** (473)204-51-73  
**Екатеринбург** (343)384-55-89

**Иваново** (4932)77-34-06  
**Ижевск** (3412)26-03-58  
**Иркутск** (395)279-98-46  
**Казань** (843)206-01-48  
**Калининград** (4012)72-03-81  
**Калуга** (4842)92-23-67  
**Кемерово** (3842)65-04-62  
**Киров** (8332)68-02-04  
**Коломна** (4966)23-41-49  
**Кострома** (4942)77-07-48  
**Краснодар** (861)203-40-90  
**Красноярск** (391)204-63-61  
**Курск** (4712)77-13-04  
**Курган** (3522)50-90-47  
**Липецк** (4742)52-20-81

**Магнитогорск** (3519)55-03-13  
**Москва** (495)268-04-70  
**Мурманск** (8152)59-64-93  
**Набережные Челны** (8552)20-53-41  
**Нижний Новгород** (831)429-08-12  
**Новокузнецк** (3843)20-46-81  
**Ноябрьск** (3496)41-32-12  
**Новосибирск** (383)227-86-73  
**Омск** (3812)21-46-40  
**Орел** (4862)44-53-42  
**Оренбург** (3532)37-68-04  
**Пенза** (8412)22-31-16  
**Петрозаводск** (8142)55-98-37  
**Псков** (8112)59-10-37  
**Пермь** (342)205-81-47

**Ростов-на-Дону** (863)308-18-15  
**Рязань** (4912)46-61-64  
**Самара** (846)206-03-16  
**Саранск** (8342)22-96-24  
**Санкт-Петербург** (812)309-46-40  
**Саратов** (845)249-38-78  
**Севастополь** (8692)22-31-93  
**Симферополь** (3652)67-13-56  
**Смоленск** (4812)29-41-54  
**Сочи** (862)225-72-31  
**Ставрополь** (8652)20-65-13  
**Сыктывкар** (8212)25-95-17  
**Тамбов** (4752)50-40-97  
**Тургут** (3462)77-98-35  
**Тверь** (4822)63-31-35

**Тольятти** (8482)63-91-07  
**Томск** (3822)98-41-53  
**Тула** (4872)74-02-29  
**Тюмень** (3452)66-21-18  
**Ульяновск** (8422)24-23-59  
**Улан-Удэ** (3012)59-97-51  
**Уфа** (347)229-48-12  
**Хабаровск** (4212)92-98-04  
**Чебоксары** (8352)28-53-07  
**Челябинск** (351)202-03-61  
**Череповец** (8202)49-02-64  
**Чита** (3022)38-34-83  
**Якутск** (4112)23-90-97  
**Ярославль** (4852)69-52-93

**Россия** (495)268-04-70

**Казахстан** (772)734-952-31

**Киргизия** (996)312-96-26-47



# Fire protection



## Fire extinguisher - CO<sub>2</sub>

For use on **class B fires**. Ideal for areas with sensitive electronic and electric equipment. Content 2 kg. With wall mount.

**Warning** H280

| Ø x H (mm) | Art. No. | Pack Qty. |  |
|------------|----------|-----------|--|
| 110 x 555  | 1028.1   | 1 unit(s) |  |



## Fire protection tub SEKUROKA®

JM-Metzger.

Tub and mesh made of chrome-nickel steel.

- Liquids are collected immediately and fire-safe in the mesh
- If the liquid ignites, the flame extinguishes autonomously due to lack of oxygen
- Resists heat and corrosion
- Liquids collected can be transferred for disposal or reuse
- The mesh can be removed and is easy to clean and reuse
- No glass or steel wool mats needed, so there is no material to dispose of
- Weight 12 kg

**Note.** The meshes may only be filled to 2/3 with flammable liquid. Maximum collection volume approx. 13 litres.

| L x W x H       | Art. No. | Pack Qty. |  |
|-----------------|----------|-----------|--|
| 450 x 450 x 120 | 1658.1   | 1 unit(s) |  |



## Safety cabinet Q-CLASSIC-90

Asecos.

For the storage of flammable liquids.

Acc. to DIN EN 14470-1, 90 min fire resistance (FWF 90). Ceric-compliant, GS approved, acc. to DIN EN 14727 (laboratory furniture).

- **Highly rugged design**, scratchproof textured paint finish
- The panel doors lock in any position for easy storage and removal from storage
- **Automatic locking of doors in the event of fire** thanks to integrated thermal release system
- Forklift-accessible base – easy transport, high flexibility, lockable with optional plinth panel
- **Easy alignment** – adjusting aids to compensate for uneven floor
- **Quick commissioning** – air ducts ready for connection (NW 75) to a technical exhaust system

### Version:

Anthracite grey body (similar to RAL 7016), light grey doors (RAL 7035), with panel doors.

Please note: Additional transport costs apply for delivery to the place of use. We will be happy to inform you of these on request.

**Delivery without** ventilation unit, recirculating air filter system and plinth panel. Optional, please order separately.

### 2-door 3 shelves

Inner fittings: 3 shelves, perforated plate insert and bottom tray (33 l)

| Door stop   | W x D x H (mm)    | Art. No. | Pack Qty. |  |
|-------------|-------------------|----------|-----------|--|
| left, right | 1193 x 615 x 1953 | CCA0.1   | 1 unit(s) |  |

### 2-door 4 full-extension drawers

Inner fittings: 4 full-extension drawers (sheet steel, powder coated)

| W x D x H (mm)    | Art. No. | Pack Qty. |  |
|-------------------|----------|-----------|--|
| 1193 x 615 x 1953 | CCA1.1   | 1 unit(s) |  |

### 2-door, 6 full-extension drawers

Inner fittings: 6 full extension drawers (sheet steel, powder coated)

| Type                     | W x D x H (mm)    | Art. No. | Pack Qty. |  |
|--------------------------|-------------------|----------|-----------|--|
| 6 Full-extension drawers | 1193 x 615 x 1953 | CCA2.1   | 1 unit(s) |  |

### 1-door, 3 shelves

Inner fittings: 3 shelves, perforated plate insert and bottom tray (22 l)

| Door stop | W x D x H (mm)   | Art. No. | Pack Qty. |  |
|-----------|------------------|----------|-----------|--|
| left      | 599 x 615 x 1953 | CCA3.1   | 1 unit(s) |  |
| right     | 599 x 615 x 1953 | CCA4.1   | 1 unit(s) |  |

### 1-door, 6 full-extension drawers

Inner fittings: 6 full extension drawers (sheet steel, powder coated)

| Door stop | W x D x H (mm)   | Art. No. | Pack Qty. |  |
|-----------|------------------|----------|-----------|--|
| left      | 599 x 615 x 1953 | CCA5.1   | 1 unit(s) |  |
| right     | 599 x 615 x 1953 | CCA6.1   | 1 unit(s) |  |

# Safety cabinets

## Accessories plinth panel for Q-CLASSIC-90 safety cabinet

Asecos.

### 1200 2-door

| Designation                      | Art. No. | Pack Qty. |  |
|----------------------------------|----------|-----------|--|
| Plinth panel for 2-door cabinets | CCA7.1   | 1 unit(s) |  |

### 600 1-door

| Designation                      | Art. No. | Pack Qty. |  |
|----------------------------------|----------|-----------|--|
| Plinth panel for 1-door cabinets | CCA8.1   | 1 unit(s) |  |



## Accessories for safety cabinet

Asecos.

### (1) Ventilation unit without exhaust monitor

Safe detection of vapour and gas emissions at the outlet or source.  
Housing made of powder-coated high-grade sheet steel.

- Plug ready – fast and easy assembly
- Extra low noise, ideal for use directly in the workspace
- NW 75 hose connection
- ATEX-compliant: Ceric II 3/-G Ex c IIC T4

**Delivery incl.** Connecting cable and mains plug.

| W x D x H (mm)  | Art. No. | Pack Qty. |  |
|-----------------|----------|-----------|--|
| 200 x 400 x 200 | CCA9.1   | 1 unit(s) |  |

### (2) Recirculating air filter system

Vents safety cabinets safely and economically without exhaust lines.  
Recirculating air filter housing made of powder-coated high-grade sheet steel.

- Installation without wall breakthroughs and exhaust lines
- Flexible selection of installation location
- Safe detection of hazardous vapours with retention in the filtration system
- Silent – only approx. 39 dB (A)
- ATEX-compliant: CE II 3/-G Ex ic nA IIB T4Gc"

**Delivery incl.** Multi-stage filter system, connection cable and mains plug, VDE-tested electronic monitoring system for monitoring exhaust air and filter, visual and audible alarm incl. potential-free alarm contact.

| W x D x H (mm)  | Art. No. | Pack Qty. |  |
|-----------------|----------|-----------|--|
| 305 x 555 x 210 | CCC0.1   | 1 unit(s) |  |



## Combi safety cabinet K-PHOENIX-90

Asecos.

**Two in one** – storage of flammable and aggressive hazardous substances in one cabinet.

Acc. to DIN EN 14470-1, 90 min fire resistance (FWF 90). Ceric-compliant, GS approved, acc. to DIN EN 14727 (laboratory furniture).

- **Rugged and durable** – safety elements assembled outside the storage compartment for increased protection against corrosion
- **Safely isolated** – storage chambers hermetically separated by central partition
- **Comfortable and safe** – doors lock in the standard stop position, safe storage and removal from storage of drums, all doors can be operated and locked separately
- **Easy alignment** – adjusting aids to compensate for uneven floor
- **Quick commissioning** – integrated air ducts ready for connection (NW 75) to a technical exhaust system

**Version:** Outer body made of epoxy resin coated high-grade sheet steel. Inner body made of highly resistant melamine resin coated special panels. Colour: Light grey (RAL 7035).

Please note: Additional transport costs apply for delivery to the place of use. We will be happy to inform you of these on request.

**Delivery without** ventilation unit (Art. no. CCA9.1). Optional, please order separately.

### (1) Inner fittings 3 shelves/4 pull-out shelves

**Left side of cabinet,** compartment for flammable liquids: with folding door, 3 shelves (75 kg load capacity), perforated sheet insert and 22 l bottom tray (powder-coated sheet steel).

**Right side of cabinet,** compartment for acids and bases: with panel doors, 4 pull-out shelves (25 kg load capacity) incl. removable plastic tray.

| W x D x H (mm)    | Art. No. | Pack Qty. |  |
|-------------------|----------|-----------|--|
| 1200 x 615 x 1968 | CCC1.1   | 1 unit(s) |  |

### (2) Inner fittings 6 full extension drawers/6 pull-out shelves

**Left side of cabinet,** compartment for flammable liquids: With folding door, 6 full extension drawers (powder-coated sheet steel).

**Right side of cabinet,** compartment for acids and bases: With panel doors, 6 pull-out shelves (25 kg load capacity) incl. removable plastic tray.

| W x D x H (mm)    | Art. No. | Pack Qty. |  |
|-------------------|----------|-----------|--|
| 1200 x 615 x 1968 | CCC2.1   | 1 unit(s) |  |



# Safety cabinets



## Acids and bases cabinet SL-Classic

Asecos.

Safe and correct storage of aggressive, non-flammable hazardous substances in work zones. GS approved, acc. to DIN EN 14727 (laboratory furniture).

- **Rugged and durable** – epoxy resin coated high-grade sheet steel, locking mechanism is located outside the store room for increased protection against corrosion
- **Safely isolated** – two hermetically separated storage chambers
- **No unauthorised use** – doors are fitted with profile cylinder locks (master-key system compatible)
- **Easy alignment** – integrated adjusting aids to compensate for uneven floor
- **Quick commissioning** – air ducts ready for connection (NW 75) to a technical exhaust system
- **Clean ventilation** – corrosion-resistant, metal-free air ducts, separate ventilation of storage chambers, only one air vent in roof area

**Equipment:** pull-out shelves – high-quality, sturdy construction with liquid-tight, removable plastic tray (18 l), 25 kg load capacity. With panel doors, colour: Light grey (RAL 7035).

Please note: Additional transport costs apply for delivery to the place of use. We will be happy to inform you of these on request.

**Delivery without** ventilation unit (Art. no. CCA9.1). Optional, please order separately.

### (1) Width 1200

With vertical centre partition: Separate storage of acids and bases. Inner fittings: 12 pull-out shelves incl. plastic collecting tray

| Door stop   | W x D x H (mm)    | Art. No. | Pack Qty. |
|-------------|-------------------|----------|-----------|
| left, right | 1197 x 603 x 1965 | CCC8.1   | 1 unit(s) |

### (2) Width 600

With horizontal centre partition: separate storage of acids and bases. Inner fittings: 6 pull-out shelves incl. plastic collecting tray

| Door stop | W x D x H (mm)   | Art. No. | Pack Qty. |
|-----------|------------------|----------|-----------|
| left      | 597 x 603 x 1965 | CCC9.1   | 1 unit(s) |
| right     | 597 x 603 x 1965 | CCE0.1   | 1 unit(s) |



## Compressed gas cylinder cabinet G90

Asecos.

For safe indoor storage of pressurised gas cylinders (decentralised). Type-tested acc. to DIN EN 14470-2, 90 min fire resistance (FWF 90). Ceric-compliant, GS approved, acc. to DIN EN 14727 (laboratory furniture).

- **Easy assembly of fittings and pipework** – large inner height (1858 mm), 24 leadthroughs in the cabinet ceiling
- **No unauthorised use** – door is fitted with profile cylinder locks (master-key system compatible)
- **Easy alignment** – adjusting aids to compensate for uneven floor
- **Quick commissioning** – integrated air ducts ready for connection (NW 75) to a technical exhaust system, complete and even floor-to-ceiling ventilation inside cabinet

**Version:** With panel door, hinge on the left. Body and door light grey (RAL 7035)

Please note: Additional transport costs apply for delivery to the place of use. We will be happy to inform you of these on request.

**Delivery incl.** standard inner fittings (mounting rails, roll-in flap, cylinder holder and suitable tensioning straps).

### (1) For 2x50 litre gas cylinders

| Pic. | Suitable for      | W x D x H (mm)   | Art. No. | Pack Qty. |
|------|-------------------|------------------|----------|-----------|
| (1)  | 2 x 50 l/3 x 10 l | 598 x 616 x 2050 | CCC3.1   | 1 unit(s) |

### (2) For 1x50 litre gas cylinder

| Pic. | Suitable for      | W x D x H (mm)   | Art. No. | Pack Qty. |
|------|-------------------|------------------|----------|-----------|
| (2)  | 1 x 50 l/2 x 10 l | 598 x 616 x 2050 | CCC4.1   | 1 unit(s) |

### (3) For 10 litre gas cylinders

| Pic. | Suitable for | W x D x H (mm)   | Art. No. | Pack Qty. |
|------|--------------|------------------|----------|-----------|
| (3)  | 2 x 10 l     | 598 x 616 x 1450 | CCC5.1   | 1 unit(s) |

## Accessories for G90 compressed gas cylinder cabinet

Asecos.

### Cylinder holder set

2 cylinder holders with 2 tensioning straps for the additional securing of small 10 l compressed gas cylinders.

| Designation         | Art. No. | Pack Qty. |
|---------------------|----------|-----------|
| Cylinder holder set | CCC6.1   | 1 set     |

### Gas cylinder trolley

For 1 x 50 l gas cylinder.

| Designation                                    | Art. No. | Pack Qty. |
|------------------------------------------------|----------|-----------|
| Gas cylinder trolley for 1 x 50 l gas cylinder | CCC7.1   | 1 unit(s) |

# Safety cabinets



## Wall cupboard SEKUROKA®

ROTH SELECTION.

Made of sheet steel. Colour: Light grey (RAL 7035).

- With two fixed shelves (distance from top: 160 and 470 mm)
- Smooth surface with no ventilation slots
- Reinforced door, hinge on the right
- DOM cylinder cam lock with 2 keys

**Delivery without** warning symbols.

| W x D x H (mm)  | Art. No. | Pack Qty. |  |
|-----------------|----------|-----------|--|
| 400 x 200 x 800 | 5226.1   | 1 unit(s) |  |



## Jumbo filter trolley

ULT Umwelt-Lufttechnik. Material: ABS, PC.

For absorbing and filtering gases and vapours directly where they arise.

### Applications:

For glueing, lacquering, laminating and absorbing solvent vapours and undertaking cleaning work.

- With wheels to enable flexible operation at different workstations
- Extremely quiet
- Three articulated arms provide flexibility
- Range of the suction arm: 750 mm
- Low energy consumption
- Ultra-filter effect results in clean air
- The filtered air is filtered back into the working area
- Filter can be easily removed for changing
- Dimensions: Cover L 296 x W 248 mm,  
Trolley L 450 x W 340 x H 530 mm

### Technical specifications:

| Art. No.          | Y928.1       |
|-------------------|--------------|
| Sound level       | 49 db        |
| Power consumption | 150 W        |
| Weight            | 18 kg        |
| Mains connection  | 230 V, 50 Hz |

| Type                          | Art. No. | Pack Qty. |  |
|-------------------------------|----------|-----------|--|
| Filter trolley Jumbo complete | Y928.1   | 1 unit(s) |  |



## Glove bag SEKUROKA®

ROTH SELECTION. Material: PE.

With integrated gloves. For carrying out work in environments free of air or moisture.

Handling: Glove bags are fed through the opening with the working utensils, closed using a clip and filled with inert gas through the gas connector. Plastic coupling for gas connector, closing clips and inner gloves are also included.

### With one opening for filling

With one hose connection for 1936.1 and K352.1, two hose connections for K353.1

| L x W x H (mm)  | Opening (mm) | Art. No. | Pack Qty. |  |
|-----------------|--------------|----------|-----------|--|
| 420 x 420 x 280 | 275          | 1936.1   | 1 unit(s) |  |
| 690 x 690 x 380 | 565          | K352.1   | 1 unit(s) |  |
| 940 x 940 x 640 | 860          | K353.1   | 1 unit(s) |  |

### With two openings for filling

Incl. two tube connections.

| L x W x H (mm)  | Opening (mm) | Art. No. | Pack Qty. |  |
|-----------------|--------------|----------|-----------|--|
| 490 x 490 x 290 | 2 x 300      | 1937.1   | 1 unit(s) |  |

**Алматы** (7273)495-231  
**Ангарск** (3955)60-70-56  
**Архангельск** (8182)63-90-72  
**Астрахань** (8512)99-46-04  
**Барнаул** (3852)73-04-60  
**Белгород** (4722)40-23-64  
**Благовещенск** (4162)22-76-07  
**Брянск** (4832)59-03-52  
**Владивосток** (423)249-28-31  
**Владикавказ** (8672)28-90-48  
**Владимир** (4922)49-43-18  
**Волгоград** (844)278-03-48  
**Вологда** (8172)26-41-59  
**Воронеж** (473)204-51-73  
**Екатеринбург** (343)384-55-89

**Иваново** (4932)77-34-06  
**Ижевск** (3412)26-03-58  
**Иркутск** (395)279-98-46  
**Казань** (843)206-01-48  
**Калининград** (4012)72-03-81  
**Калуга** (4842)92-23-67  
**Кемерово** (3842)65-04-62  
**Киров** (8332)68-02-04  
**Коломна** (4966)23-41-49  
**Кострома** (4942)77-07-48  
**Краснодар** (861 )203-40-90  
**Красноярск** (391)204-63-61  
**Курск** (4712)77-13-04  
**Курган** (3522)50-90-47  
**Липецк** (4742)52-20-81

**Россия** (495)268-04-70

**Магнитогорск** (3519)55-03-13  
**Москва** (495)268-04-70  
**Мурманск** (8152)59-64-93  
**Набережные Челны** (8552)20-53-41  
**Нижний Новгород** (831)429-08-12  
**Новокузнецк** (3843)20-46-81  
**Ноябрьск** (3496)41-32-12  
**Новосибирск** (383)227-86-73  
**Омск** (3812)21-46-40  
**Орел** (4862)44-53-42  
**Оренбург** (3532)37-68-04  
**Пенза** (8412)22-31-16  
**Петрозаводск** (8142)55-98-37  
**Псков** (8112)59-10-37  
**Пермь** (342)205-81-47

**Казахстан** (772)734-952-31

**Ростов-на-Дону** (863)308-18-15  
**Рязань** (4912)46-61-64  
**Самара** (846)206-03-16  
**Саранск** (8342)22-96-24  
**Санкт-Петербург** (812)309-46-40  
**Саратов** (845)249-38-78  
**Севастополь** (8692)22-31-93  
**Симферополь** (3652)67-13-56  
**Смоленск** (4812)29-41-54  
**Сочи** (862)225-72-31  
**Ставрополь** (8652)20-65-13  
**Сыктывкар** (8212)25-95-17  
**Тамбов** (4752)50-40-97  
**Сургут** (3462)77-98-35  
**Тверь** (4822)63-31-35

**Киргизия** (996)312-96-26-47

**Тольятти** (8482)63-91-07  
**Томск** (3822)98-41-53  
**Тула** (4872)74-02-29  
**Тюмень** (3452)66-21-18  
**Ульяновск** (8422)24-23-59  
**Улан-Удэ** (3012)59-97-51  
**Уфа** (347)229-48-12  
**Хабаровск** (4212)92-98-04  
**Чебоксары** (8352)28-53-07  
**Челябинск** (351 )202-03-61  
**Череповец** (8202)49-02-64  
**Чита** (3022)38-34-83  
**Якутск** (4112)23-90-97  
**Ярославль** (4852)69-52-93